



Crimping Line

Micrograph laboratory Microlab ML 3700

Tabletop laboratory for making cross-section analysis



With the Microlab you can prepare microsections of crimped contacts in a very professional and comfortable manner.

The Microlab product family is designed to prepare cross sections of conductor crimps and insulation crimps easily and comfortably within a few minutes. After cutting, polishing and etching of the sample, the image of the cross section can be visualized on the screen. Now a comprehensive quality check of the crimp can be performed by using the special designed image processing software X-Scan.

Equipped with a high quality 12x zoom objective the **Microlab ML 3700** is the ideal tool to conduct quality tests quick and comfortable. The high resolution camera delivers first-class digital colour pictures which can be easily measured with the automatic function of the image processing software **X-Scan**. Automatically generated records can be used as proofs of Of course, X-Scan fulfills all relevant DIN standards and OEM specifications. quality.

Performance features

- Complete micrograph laboratory integrated in an MDF board
- Easily operated optic with 12x zoom objective with an outstanding combination of zoom and resolution
- First-class digital colour camera USB 3.0 with special photosensitive CMOS sensor and 5.0 megapixel resolution
- Well suited for cross sections from **0.1 to 10 mm**² (AWG 28 AWG 10)
- Comfortable analysis software X-Scan



C-tec Cable technologies GmbH & Co.KG

Ilztalstraße 11 Tel.: +49 (0) 8554 - 94 23 9-0 D-94513 Schoenberg Fax: +49 (0) 8554 - 94 23 9-20

eMail: info@cable-tec.net www.cable-tec.net





Crimping Line



Terminal holder



Finished microsection with X-Scan



Optic with camera



Cut control with an optional Cut Camera (VCS)

Performance features in detail

- Complete system, integrated ergonomically and functionally in an MDF board laminated with stainless steel
- High quality optic with 12x zoom objective and convenient focusing (coarse and fine adjustment)
- High performance digital color camera with photosensitive 5.0 megapixel CMOS-Sensor, optical class 1/2", USB 3.0
- Suitable for small and medium contact sizes from 0.1 to 10 mm²
- Standard terminal holder for **cross sections up to 6 mm²** (further sizes available on request)
- Dong-life **LED illumination** at the microscope
- Energy saving working lamp for the Cutting-/Grinding unit
- Fitting gas tight mount for 7 calibration gauges
- Appropriate tool set for the sample preparation
- With comfortable analysis software X-Scan
- Software calibration based on traceable standards incl. calibration certificate
- © Cross-sectioning of the sample can be carried out without any disturbance of the terminal and cable stranding
- Optional: integrated Cut Camera (VCS) for exact cut control, easily operated by touch display
- Optional: **ancillary lens 0.5x** for 12x zoom objective for extended applications

Specifications

- Type
- Voltage supply
- Smallest extension (15" monitor)
- Largest extension (15" monitor)
- Smallest crimp height for a full screen
- Dargest crimp height for a full screen
- Measurement resolution µm per pixel
- Optical zoom grades
- Camera resolution
- Camera connection
- Object illumination
- Fine polishing
- Cross section sizes standard
- Recommended temperature
- Dimensions (W x D x H)
- Weight

ML 3700

100 - 240 VAC 50/60 Hz

24x

288x

0.25 mm

8.0 mm

13 - 7.31 - 5.17 - 3.72 - 3.0 - 2.45 - 2.10 - 1.84 - 1.64 - 1.47 - 1.34 - 1.23 - 1.14 - 1.06

0.58 - 1.0 - 1.5 - 2.0 - 2.5 - 3.0 - 3.5 - 4.0 - 4.5 - 5.0 - 5.5 - 6.0 - 6.5 - 7.0

2560 x 1920 Pixel

USB 3.0 port

Longlife LED ring light for true color pictures

electro chemical

0.1mm² - 10mm² (AWG 28 – AWG 10)

22°C +/- 5°

1200mm x 500mm x 570mm

32 kg



C-tec Cable technologies GmbH & Co.KG

Ilztalstraße 11 Tel.: +49 (0) 8554 – 94 23 9-0 eMail: info@cable-tec.net D-94513 Schoenberg Fax: +49 (0) 8554 – 94 23 9-20 www.cable-tec.net